

## FEATURES

- Lightweight yet highly durable
- High lumen output of 9000lm
- Comes with stainless steel 304 clips for easy installation
- Ideal for use in a wide range of environments

## RS PRO 80 W LED Ceiling Light Batten, 100 → 277 V ac LED Non Corrosive Fitting, 1 Lamp, 1.5 m Long, IP65

RS Stock No.: 183-0588



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This high quality 5ft 80W LED NCF light batten from RS PRO features a high lumen output of 9000lm and is ideal for industrial and commercial applications such as warehouses, car parks, arenas, wet areas and more. The light consists of a polycarbonate body and diffuser with an aluminium tray construction, ensuring a lightweight yet highly durable light suitable for a wide range of environments.

## General Specifications

<b>Type</b>	LED Non Corrosive Fitting
<b>Number Of Lamps</b>	1
<b>Colour Tone</b>	Daylight
<b>Lamp Type</b>	LED
<b>Colour Temperature</b>	6300K
<b>Anti-Corrosive</b>	No
<b>PIR Included</b>	No
<b>Applications</b>	Ceiling lights are a very common type of light fixture which can be fitted to the ceiling in: Industrial areas; Multi-storey car parks; Workshops, warehouses and factories; Garages
<b>Dimmable</b>	No

## Electrical Specifications

<b>Wattage</b>	80W
<b>Voltage Rating</b>	100V to 277V

**Mechanical Specifications**

Length	1.5m
Width	94mm
Beam Angle	120°
Lumen Output	9000lm +/-10%
Ra	>70
Lumen Efficiency	100Lm/W +/-10%

**Operation Environment Specifications**

Temperature	-25°C to 50°C
-------------	---------------

**Protection Category**

IP Rating	IP65
IK Rating	IK08

**Approvals**

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------



