

Product Information



DYR125x37-Ø12

EAN 4031582318296

Wheel centre made of pressed steel, Tread: solid rubber, black, electric conductive, roller bearing

Technical Data

Wheel diameter	125 mm
Width of Tread	37 mm
Axle Hole-Ø	12 mm
Hub length	44.4 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.562 kg
Hardness of tread	Shore A 80
Load capacity	100 kg
Load capacity (static)	200 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

