

FEATURES

- A2 stainless steel construction for durability
- BS4320
- Available in a range of metric sizes

Stainless Steel Plain Washer, 2mm Thickness, M16 (Form B), A2 304

RS Stock No.: 275-715



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO Brand, these stainless steel washers are generally used with a machine threaded fastener and nut to spread the load over a greater surface area when tightening a bolt, screw or nut. As they are made of stainless steel, they have an element of corrosion resistance and are suitable for use in many environments.

General Specifications

For Screw/Bolt Size	M16 (Form B)
Material	Stainless Steel
Finish	Plain
Application	Commonly used in many electronic, food, chemical and construction applications

Mechanical Specifications

Inside Diameter	17mm
Outside Diameter	30mm
Stainless Steel Type	A2 302
Thickness	2mm

Approvals

Compliance/Certifications	BS4320
----------------------------------	--------



RS Part No.	Thread Size	Inside Diameter	Outside Diameter
189664	M8	6.4mm	12.5mm
189670	M10	10.5mm	21mm
275715	M16	17mm	30mm
275721	M20	21mm	37mm
530797	M8	8.4mm	17mm
530804	M10	10.5mm	21mm
530810	M12	13mm	24mm
1839051	M12	13mm	24mm
2484618	M16	17mm	30mm
2484624	M20	21mm	37mm