

## 306 75

### Ring slogging spanner

|                       |             |
|-----------------------|-------------|
| Code                  | ETIM        |
| 6476320               | EC002188    |
| EAN                   | UNSPSC      |
| 4010886647639         | 27-11-17-05 |
| Country of origin     | eCl@ss      |
| Germany               | 21-04-01-03 |
| Customs tariff number |             |
| 82041100              |             |



### Article description

- Top-grade industrial quality for the hardest of continuous use
- For heavy-duty work
- Special sizes available on request up to 250 mm
- Up to length 435 mm made of chrome vanadium steel 31CrV3, from length 480 mm made of material C35
- \* not standardised
- Acc. to DIN 7444

### Article information

|                          |         |                           |          |
|--------------------------|---------|---------------------------|----------|
| Contents (Qty of pieces) | 1       | Standard                  | DIN 7444 |
| Net weight [kg]          | 3,01 kg | Width across flats 1 [mm] | 75       |
| Total length [mm]        | 325 mm  | Head height 1 [mm]        | 34 mm    |
| Surface                  | oiled   | Width of head 1 [mm]      | 114,5 mm |
| Material                 | 31CrV3  | Ring profile              | bi-hex   |