



Notice : 1545 150 PA CH

GUYARD SAS

22-24, rue Lucien Rouzet
Z.A. Villedieu sur Indre/Niherne
36250 NIHERNE FRANCE

Index : 2

FEATURES :

- 5 finger glove in natural goatskin leather.
- 150 mm natural crust leather cuff.
- Artery protection.
- Aramid thread seams.
- Chrome-tanned, length from 35 to 39 cm depending on size

AVAILABLE SIZES :

- Size 6 to 12.

PRECAUTIONS FOR USE :

- Wear the gloves on dry and clean hands. It is recommended to test the gloves first. Actual use conditions may be different from the EU type tests.
- Before reusing, check the gloves for defects, holes, tears, unusual wear, etc.
- Expiration date : 5 years from the date of manufacture stated on the glove.

SAFETY COMFORT AND DEXTERITY :

- Dexterity level 5.
- The glove does not contain substances at levels which are known or suspected to have harmful effects on the hygiene or health of the user under the expected conditions of use.

PACKAGING :

- In case of unpacking, a copy of the instruction sheet must be enclosed with the next smallest package.
- Bag of 10 pairs.
- Box of 100 pairs.

MARKING :

- The CE marking on this glove indicates compliance with the essential health and safety requirements of the European regulation 2016/425 on personal protective equipment (PPE).
- **RECOMMENDED USES:**
 - Gloves designed for welding work.

Intermediate risks - Category II PPE

EN 420 :2003 +A1 :2009 EN 388 :2016

EN 407 : 2004 EN ISO 13997 :1999

EN 12477 :2001 +A1 :2005 Type B

EN 420 :2003+A1 :2009

EN 388 :2016

EN 407 :2004



2 1 2 1 B



4 1 1 2 4 X

PERFORMANCE LEVELS :

EN 388 :2016

- | | |
|--|-----|
| • Abrasion : | 2/4 |
| • Blade cut : | 1/5 |
| • Tear : | 2/4 |
| • Puncture : | 1/4 |
| • Cutting by sharp objects (ISO 13997) : | B/F |
| • <u>EN 407 :2004</u> | |
| • Flame behavior : | 4/4 |
| • Contact heat : | 1/4 |
| • Convective heat : | 1/4 |
| • Radiant heat : | 2/4 |
| • Small splashes of liquid metal : | 4/4 |
| • Large splashes of liquid metal : | X |

EN 12477 :2001+ A1 /2005

- | | |
|----------|---|
| • Type : | B |
|----------|---|

PROTECTION LIMITS :

- Do not use for handling objects with a temperature higher than 100°C.
- Do not use for handling chemical products.

MAINTENANCE AND STORAGE

- No special maintenance is recommended. It is advisable to store the products in a cool, dry and ventilated place, keep away from light.

END OF LIFE

- End-of-life destruction must be controlled and comply with European traceability and environmental requirements.

EU type certificate issued in accordance with module B Regulation (EU) 2016/425

LEITAT ON n° :0162

The EU declaration of conformity is available on

www.guyard-sa.com