





RECOMMENDED STRIP LENGTH



1. SEE I.S. 1914-2

RG-174/U & 188/U	30.48 [1.200]	220009-1	21427-2	9-328666-0	1-331368-2	2-331355-5	5225396-7
RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	30.48 [1.200]	69477-1	-	9-50428-0	2-331368-3	2-331355-4	5225396-2
RG-58/U,58A/U,58B/U & 58C/U	30.48 [1.200]	69478-1	-	9-50427-1	1-331369-6	2-331355-3	5225396-1
CABLE SIZE	A	CRIMP TOOL	4 BUSHING QTY=1	3 FERRULE QTY=1	2 CONTACT QTY=1	1 JACK ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
-

DWN
A. FERNANDEZ-DOCK5
31JAN2005

CHK
J. HAVENER
31JAN2005

APVD
J. LIPPERT
31JAN2005

PRODUCT SPEC
108-12020

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
JACK, DUAL CRIMP,
SERIES BNC

SIZE
A1

CAGE CODE
00779

DRAWING NO
5225396

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
P

TE Connectivity