

EcoFlow RIVER 3 Plus power station: 286Wh, 600W (X-Boost 1200W), expandable to 858Wh, 1h recharge, UPS <10ms, ideal for camping and emergency use.

BOX CONTENTS: 1 EcoFlow RIVER 3 Plus – 600W, 858Wh

Expandable Electric Charging Station

1 AC Charging Cable

1 USB-B Communication Cable

1 Cigarette Lighter Charging Cable

YOUR RELIABLE COMPANION DURING POWER OUTAGES OR ON THE GO Up to 600W output power

Expandable capacity up to 858Wh

Fast charging in 1 hour (without damaging the battery)

16 additional hours of battery life for devices consuming less than 100W

Transfer time < 10ms

Noise level < 30dB LFP technology offering 3000 charge cycles and up to 10 years of daily use

Operating Time of Your Devices:

Travel Router (10W): 20.4 h

Drone (40W): 5.8 h

Car Refrigerator (60W): 3.9 to 6 h

Game Console (100W): 2.2 h

Refrigerator (120W): 1.9 h

Computer (600W): 20 min

THE RIVER 3 PLUS IN DETAIL

Wireless Connection - Equipped with Pogo pins, the RIVER 3 Plus connects instantly to compatible additional batteries, without cables or screws.

This allows you to easily increase its capacity.

An Additional Charging and Recharging Option –

The additional batteries in this range feature a USB-C port, giving you an additional fast charging and recharging option with a power output of 140W. Versatile, they can also...

Waterproof, flame-retardant, and shockproof design – IP54 certified, the battery pack is protected against water damage. Its robust, flame-retardant casing withstands harsh conditions. Even after a one-meter drop, the device will not be damaged.

LiFePO₄ cells, up to 10 years of daily use – The RIVER 3 Plus has a lifespan of 3,000 charge cycles. This equates to approximately 10 years of daily use before its rated capacity is reduced to 80...

X-Guard Battery Protection Technology - Thanks to its advanced cloud-based monitoring algorithm, the RIVER 3 Plus continuously analyzes over 40 safety parameters. It protects your devices against current and voltage fluctuations, temperature variations, and short-circuit risks, ensuring reliable and safe operation.

COMPATIBLE WITH 90% OF YOUR ELECTRICAL DEVICES Up to 1200W of output power with X-Boost - Compact, powerful, built to last. The RIVER 3 Plus is a true benchmark in the world of portable batteries, offering a nominal power of 600W. In X-Boost mode, it goes even further, delivering up to 1200W continuously. That's enough to power 90% of your electrical devices, even the most energy-intensive ones, like a heater. And thanks to its integrated light, you...

4 CHARGING OPTIONS

Get ready for outdoor adventures and power outages quickly with its fast-charging technology.

Solar charging: 100% charge in 1.5 hours - The RIVER 3 Plus can accept up to 220W of solar input power to fully recharge in just 1.5 hours. For even greater portability, pair it with our ultra-compact 45W solar panel. Equipped with a USB-C port, it can directly charge your electronic devices.

Mains charging: 100% charge in 1 hour - Thanks to X-Stream technology, the RIVER 3 Plus recharges from the mains in just 1 hour. Revolutionary speed, without compromising its longevity. Its secret? Robust lithium-ion cells, designed to the same quality standards as electric vehicle batteries. To preserve their performance over time, a maintenance charging technology precisely adjusts each charging cycle, limiting wear and tear....

Car charging: 100% charge in 3.3 hours - Plug the RIVER 3 Plus into your car's cigarette lighter socket for fast charging on the go. Generator charging: 100% charge in 1 hour - Recharge the RIVER 3 Plus in just 1 hour using a gasoline generator and enjoy quiet, safe, and efficient range all day long.

OPTIMAL PROTECTION FOR YOUR SENSITIVE DEVICES

Reliable power for remote work and gaming. The RIVER 3 Plus offers advanced protection for your sensitive devices in the event of a power outage, switching to backup power in less than 10 ms. Its responsiveness prevents sudden power cuts and thus protects your equipment.

PREVENT DATA LOSS

Gain precious minutes to secure your data and safely shut down devices. With a 286 Wh capacity and a rated output of 600 W, the RIVER 3 Plus ensures your essential equipment runs smoothly. It can power a 3 W router for 35 hours, guaranteeing a stable internet connection even during outages. It also supports most office devices, including a computer consuming up to 600W, providing them with at least 21 minutes of battery life. This gives you time to save your work, safely shut down your devices, and prevent any data loss.

Smart alerts and notifications:

The RIVER 3 Plus alerts you to power failures via indicator lights, notifications in the EcoFlow app, and software alerts. Its management interface, compatible with PCs and NAS devices, along with the EcoFlow software, monitors the battery level in real time, warns you when the battery is low, and automatically records data on supported devices.

Continuous power with a practical design.

The battery is equipped with two AC outlets located on the back, allowing you to plug in your devices while keeping cables organized and discreet. Its new integrated screen displays the status of the backup power system in real time, giving you clear and intuitive control.

EXTENDED BATTERY LIFE FOR YOUR SMALL DEVICES

Face power outages with complete peace of mind and enjoy longer stays outdoors. Thanks to X-GaN Power technology, the RIVER 3 Plus combines a compact size, quiet operation, and exceptional energy efficiency. It offers up to twice the battery life for low-power devices, such as lamps and routers, redefining industry standards.

ULTRA-COMPACT AND LIGHTWEIGHT DESIGN

Your portable power source. The technology used minimizes heat loss during battery operation, thus reducing the space required for cooling. This allowed the RIVER 3 Plus to be designed in an ultra-compact format. It fits easily into small spaces such as a closet, minivan, or bag, ensuring easy storage and portability.

NOISE LEVEL BELOW 30 dB

Quiet operation day and night for absolute comfort.

Thanks to X-GaN Power heat dissipation technology, the RIVER 3 Plus emits less than 30 dB at 0.5 m, a noise level comparable to that of a library. You'll have guaranteed peace and quiet day and night, even when the system is running continuously.

OPTIMIZED CONTROL FOR SMART MANAGEMENT

Enjoy convenient, intelligent control tailored to your needs.

Real-time monitoring: Thanks to its high-visibility color display and the enhanced EcoFlow app, the RIVER 3 Plus provides detailed information on charge status and battery, giving you precise tracking at all times.

Customizable settings:

The optimized app allows you to easily adjust charging parameters, including charging speed, charge cycle scheduling, power-saving mode, and low battery alerts.

Remote control

Control your battery remotely via Wi-Fi connection when you're on the go.

PORTS (INPUTS)

1 AC Port: 200 to 240 V | 6 A | 50/60 Hz | 360 W | 100% charge in 60 minutes

1 DC Cigarette Lighter Port: 11 to 55 V | 100% charge in 3.3 hours

1 Solar Port: 11 to 55 V | 13 A | 220 W | 100% charge in 1.5 hours

PORTS (OUTPUTS)

3 AC Ports: 600W total (1200W peak) | 1200W output power with X-Boost

1 DC Cigarette Lighter Port: 12.6V | 10A | 126W max

1 USB-C Port: 5/9/12/15V - 3A max | 20V - 5A max | 100W max per port

2 USB-A Ports: 5V - 2.4A | 12W max per port | 24W total

LiFePO4 (LFP) Battery –

Battery Capacity: 286 Wh –

Shelf Life: 80% Capacity or More after 3000 cycles –

Battery Dimensions: 23.4 x 23.2 x 14.6 cm –

Optimal Operating Temperature: 20°C to 30°C –

Discharge Temperature: -10°C to 45°C –

Charge Temperature: 0°C to 45°C –

Storage Temperature: -10°C to 45°C –

App Control: Yes - Wi-Fi

Weight 4.7 kg

Noise level < 30 dB Transfer time < 10 ms (ASI)

Main color: Black

By Activity

Camping Backup Battery |

Daily Emergency

Outdoor Activities

Professional

Leisure

Compact size, ideal for :

Portable speakers

Gaming consoles

Drones

POV cameras,

Onboard cameras

DSLR cameras,

Laptops

Smartphones, and tablets.

Wi-Fi frequency: 2.4 GHz.

Max power: X-Boost 1200 W

EAN code: 4895251627917

Battery - Battery Capacity: 286 Wh - Shelf Life: 80% Capacity or More after 3000 cycles -
Battery Dimensions: 23.4 x 23.2 x 14.6 cm - Optimal Operating Temperature: 20°C to
30°C - Discharge Temperature: -10°C to 45°C - Charge Temperature: 0°C to 45°C -
Storage Temperature: -10°C to 45°C