

EC Declaration of Conformity

in accordance with EC Machinery Directive 2006/42/EC

Certificate Number: CC4-2017102500416
Location of Issue: Crosby Europe (UK) Ltd.
Station Street, Cradley Heath
West Midlands B64 6AJ, United Kingdom
Phone: 01226 290516 Fax: 01226 240118

Stock No: 1018473

Description of Gear: G209 3-1/4t Screw Pin Anchor Shackle 5/8" Maxtough®

Working Load Limit: 3-1/4t Max. Allowed Proof Load: 6-1/2t

t indicates metric tonnes

Comments: Minimum ultimate strength is 6 times the WLL

Note: Meets the performance requirements of Federal Specification RR-C-271F Type IVA, Grade A, Class 2, except for those provisions required of the contractor. Meets the requirements of EN 13889. Forged steel shackles for general lifting purposes. Dee shackles and bow shackles - Grade 6 - Safety. This equipment can meet the requirements of DNV Certification Note 2.7-1, as per DNV Certificate for type approval No S-8357.

We hereby declare that the above mentioned product with CE marking complies with the applicable essential Health and Safety requirements of the EC Machinery Directive 2006/42/EC.

Crosby forged shackles can be used in general service with good rigging practice down to temperatures of -40 °F (-40 °C).

Has not been contaminated by Mercury or Asbestos in the manufacturing process.

Number of Pieces: 1 Bow: 90G

PICs are based on visual observation

Certificate based on item being the Crosby product described above.

We hereby certify that the above described material was manufactured and processed in a manner compatible to meeting the load ratings when used under normal and proper applications.

Mentioned products are in conformity to the Crosby literature available at time of manufacturing, including the following trademarked features:



For Product Delivered To: CERTEX UK
UNIT C1 HARWORTH IND ESTATE
BRYANS CLOSE, HARWORTH
HARWORTH United Kingdom

Date: October 25, 2017
Date of Issuance

Signature:
Arn Smolderen, Quality Assurance