


URELG 3-PMTK - Basic terminal block



2820709

<https://www.phoenixcontact.com/in/products/2820709>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic terminal blocks with test pick-off on both sides and knife disconnection for NS 32 and NS 35/7,5 DIN rail, with end cover, for ST-REL..., ST-OV..., and ST-OE... plugs, 3-pos.

Commercial data

Item number	2820709
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CK6
Product key	DK61B4
Catalog page	Page 95 (IF-2005)
GTIN	4017918076832
Weight per piece (including packing)	62.94 g
Weight per piece (excluding packing)	62.94 g
Customs tariff number	85369010
Country of origin	PL

URELG 3-PMTK - Basic terminal block

2820709

<https://www.phoenixcontact.com/in/products/2820709>

Technical data

Product properties

Product type	Relay socket
Number of positions	3


Electrical properties

Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)

Connection data

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 4 mm ²
Conductor cross section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	20.8 mm (with cover)
Height	86.5 mm
Depth	109.5 mm
	114.5 mm (with NS 32 coupling connector)
	117 mm (with NS 35/15 coupling connector)

Material specifications

Color	gray (RAL 7042)
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

URELG 3-PMTK - Basic terminal block


2820709

<https://www.phoenixcontact.com/in/products/2820709>



Drawings

Schematic diagram



- 1 = Coupling connector
- 2 = Coding
- 3 = Cover
- 4 = Basic termination block


URELG 3-PMTK - Basic terminal block

2820709

<https://www.phoenixcontact.com/in/products/2820709>



Dimensional drawing




URELG 3-PMTK - Basic terminal block

2820709

<https://www.phoenixcontact.com/in/products/2820709>



Schematic diagram



1-3 = fixed bridge, cross connection rail, spacer

URELG 3-PMTK - Basic terminal block



2820709

<https://www.phoenixcontact.com/in/products/2820709>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2820709>

DNV

Approval ID: TAE00001CT



CSA

Approval ID: 13631

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	300 V	11 A	28 - 12	-



cUL Recognized

Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	300 V	10 A	30 - 12	-



UL Recognized

Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	300 V	10 A	30 - 12	-



EAC

Approval ID: RU C-DE.A*30.B.01742

cULus Recognized

URELG 3-PMTK - Basic terminal block



2820709

<https://www.phoenixcontact.com/in/products/2820709>

Classifications

ECLASS

ECLASS-11.0	27371603
ECLASS-12.0	27371603
ECLASS-13.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4d54375a-7b5a-42c7-842f-a396821ba628

URELG 3-PMTK - Basic terminal block



2820709

<https://www.phoenixcontact.com/in/products/2820709>

Accessories

DB 50- 90 BU - Wire bridge

2821180

<https://www.phoenixcontact.com/in/products/2821180>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: blue



DB 50- 90 BK - Wire bridge

2820916

<https://www.phoenixcontact.com/in/products/2820916>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: black



URELG 3-PMTK - Basic terminal block

2820709

<https://www.phoenixcontact.com/in/products/2820709>



DB 50- 90 GY - Wire bridge

2820929

<https://www.phoenixcontact.com/in/products/2820929>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: gray



E/UK - End bracket

1201442

<https://www.phoenixcontact.com/in/products/1201442>

End bracket, Mounting on a DIN rail NS 32 or NS 35, material: PA, color: gray



URELG 3-PMTK - Basic terminal block



2820709

<https://www.phoenixcontact.com/in/products/2820709>

FB-150 METER - Fixed bridge

0201595

<https://www.phoenixcontact.com/in/products/0201595>



Cross connection rail, for fixed bridging of identical inputs and outputs, made of Cu, nickel-plated, 1 m long

ZSR - Screw

2303608

<https://www.phoenixcontact.com/in/products/2303608>



Screw

URELG 3-PMTK - Basic terminal block

2820709

<https://www.phoenixcontact.com/in/products/2820709>



RPS - Reducing plug

0201647

<https://www.phoenixcontact.com/in/products/0201647>

Reducing plug, number of positions: 1, color: gray



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in