TO 4 A 12 V DC

PRODUCT FEATURES


- → Dust and water protection actuator and terminal side
- → Ice-proof lever bearing
- → Small size, large travels
- → High switching reliability due to great contact forces directly after switching
- → Series with different fastening possibilities


ON REQUEST

- → Customized assembly with connecting plugs
- → Other auxiliary actuators

10E4
< 100 m0hm (1 A 12 V DC)
> 100 M0hm (500 V DC)
250 PTI
IP 67
-40 °C +85 °C
UL 94 V-2
POM / silicone rubber stainless steel spring steel PBTP
< 5 ms
< 3 mm
gold plated
500 mm long (terminal wires 0.5 mm² molded with switch, tinned wire ends)








Basic type 1022


7

with pushbutton

L01: straight lever and snap pin







Basic type 1022

L21: simulated roller lever, on centering pin and a metal eye.

With the elongated hole fastening the switch can be swiveled around the pin and then fixed with a screw. This makes the operating position adjustable by ± 2 mm.