

# TCT saw blade (MP) 190mmx60T

## D-65595



### TECHNICAL SPECIFICATIONS

Bore (B)	30 mm
Diameter (D)	190 mm
Kerf (K)	2.2 mm
Rake (R)	5 °
Thickness (T mm )	1.4 mm
Tooth Count	60
Machine Type	Circular / Mitre Saw

### USER BENEFITS

- Can cut Aluminium, MDF, PVC, and Laminated Chipboard.
- Easy straight cutting thanks to TCG teeth type, a combination of flat and trapezoidal teeth
- Tungsten Carbide Tipped (TCT)

