

Powerfit S300

Nominal Capacity	C ₂₀ ; 1.75Vpc; @ 20°C
Float charge voltage	2.27Vpc @ 20°C
Lead alloy	Pb-Ca
Container Material	ABS (UL94-V0)
Float Life	up to 5 years @ 20°C
Self discharge	3% per month @20°C
Shelf life	9 month @ 20°C to 30°C
Operating temperature	-15°C to +50°C
Valve opening pressure	7 to 10 PSI (480 – 690 mbar)
Recombination rate	99%
Deep discharge resistant	acc. to DIN 43539 part 5