



1200 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Easy open double-throw latches
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1200
Standard



1200NF
No Foam



1200WF
With Foam

DIMENSIONS

Interior (L×W×D)	9.31 x 7.13" x 4.12 (23.6 x 18.1 x 10.5 cm)
Exterior (L×W×D)	10.67 x 9.75" x 4.86 (27.1 x 24.8 x 12.3 cm)
Lid Depth	1.18" (3 cm)
Bottom Depth	2.93" (7.4 cm)
Total Depth	4.11" (10.4 cm)
Int Volume	0.16 ft ³ (0.005 m ³)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS



Desert Tan

Orange

Silver

WEIGHT

Weight With Foam	2.87 lbs (1.3 kg)
Weight Empty	2.65 lbs (1.2 kg)
Buoyancy	12.02 lbs (5.5 kg)
Master Pack Weight	25.00 lbs (11.3 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Master Pack	6
Military	yes

ACCESSORIES



1201
3 pc. Replacement Foam Set



1203
Replacement O-ring



1200PF
Special Application Panel
Frame



1507
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 05-09-25