

ENGLISH

RS Part Number: **773-7964** Specifications and dimensions





- Boxed isolator 4 pole
- ABS plastic enclosure with padlockable handle
- · Oversized enclosure to facilitate wiring

| Specifications | |
|---|-------------------|
| Height | 175 mm |
| Width | 125 mm |
| Depth | 90 mm |
| Depth including switch | 134 mm |
| Degree of protection | IP65 |
| Rated operational current le AC21A | 32 A |
| Rated operational current le AC22A | 25 A |
| Rated operational voltage Ue IEC & EN | 690 V |
| Rated operational power AC23A 380-440V | 15 kW |
| Rated operational power AC3 440V | 11 kW |
| Maximum gL fuse size IEC | 32 A |
| Rated fused short circuit capacity IEC | 30 kA |
| Knockout size | 20 mm |
| Normal operating temperature | -25°C to +40°C |
| Maximum cable capacity | 6 mm ² |
| Recommended tightening torque | 1.7 Nm |
| Number of possible auxilliary contacts | 1 |
| Related products | |
| Neutral contact (early make/late break) | 466-295 |