

## Technical data sheet

Article number:  
151-01390

RCB180SM10



|                                  |                                                                                                         |
|----------------------------------|---------------------------------------------------------------------------------------------------------|
| <b>Product Group</b>             | Ratchet P-Clamp                                                                                         |
| <b>Product Family</b>            | For bundle diameters from 12.7 mm to 19.5 mm, B-Series                                                  |
| <b>Material</b>                  | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Steel (ST), Zinc plated (ZN) |
| <b>Colour</b>                    | Black (BK)                                                                                              |
| <b>Bundle Ø max.</b>             | 19.5 mm                                                                                                 |
| <b>Bundle Ø min.</b>             | 12.7 mm                                                                                                 |
| <b>CE Certification</b>          | No                                                                                                      |
| <b>Fixation Method</b>           | Screw Mounting                                                                                          |
| <b>Flammability</b>              | UL 94 HB                                                                                                |
| <b>for Hole Ø (FH)</b>           | 10.29 mm                                                                                                |
| <b>Length (L)</b>                | 116.2 mm                                                                                                |
| <b>Length (L2)</b>               | 83.1 mm                                                                                                 |
| <b>Min.Tensile Strength</b>      | 445 N                                                                                                   |
| <b>Operating Temperature</b>     | -40 °C to +105 °C                                                                                       |
| <b>Package Content</b>           | 280 pcs.                                                                                                |
| <b>Package Content packed in</b> | pack                                                                                                    |
| <b>ROHS compliant</b>            | Yes                                                                                                     |
| <b>UL-File Number</b>            | E64139                                                                                                  |
| <b>UV-Stabilised</b>             | Yes                                                                                                     |
| <b>Variant</b>                   | Short                                                                                                   |
| <b>Width (W)</b>                 | 34.9 mm                                                                                                 |

