



Part Number : [348996010](#)
Product Description : MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 6 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 1, Key A
Series Number : 34899
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents & Resources

Drawings


- [348996010 sd.pdf](#)
- [PK-31301-898-000.pdf](#)
- [PK-31300-635-001.pdf](#)
- [PK-31301-898-001.pdf](#)

Specifications

- [AS-34900-0001-001.pdf](#)
- [AS-34900-0001-CH-001.pdf](#)
- [PS-34900-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	34899
Description	MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 6 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 1, Key A
Application	Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Product Name	MXP120 Sealed
UPC	887191166537

Physical

Circuits (maximum)	6
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon

Net Weight	7.150/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarization	A
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
MXP120 Sealed Receptacle Housings	<u>34900</u>

Use with Part(s)

Description	Part Number
Use With	1.2 CB SWS from Tyco; For Backshells, Contact Molex

Application Tooling

Global

Description	Part Number
Extraction Tool for MXP120 Sealed Male Blade Connector	<u>638242900</u>
Extraction Toolkit for MXP120 Sealed Connection System	<u>638246300</u>