

M12 BPRT-201X | M12™ sub compact rivet tool



- Up to 325 x 4.8 mm stainless steel rivets on a single charge with a 2.0 Ah battery pack
- Suitable for all aluminium, steel, stainless steel and copper rivets up to 4.8 mm
- Rivets in one stroke with a 20.32 mm stroke length
- Retention nose pieces hold rivets in any orientation
- Tool-free access to easily clean jaws. On-board nose piece storage and removal tool for user convenience
- On board fuel gauge and LED light for added user convenience and illumination in low lit working conditions
- Ergonomic design with 273 mm H x 66.8 mm W x 165 mm in length without mandrel collector

Max. pulling force (N)	9000
Rivet diameter range (mm)	2.4 - 4.8
Stroke length (mm)	20.32
Dimensions (mm)	273 x 66 x 8 x 230
Weight with battery pack (kg)	2.1
Kit included	1 x 2.0 Ah Battery pack, C12 C Charger, HD Box
Article Number	4933464405