

251A - PRECISION SLEEVED DRIFT PUNCHES | 251A.1,5



Description

- The centre slides within a guide to prevent distortion, even in smaller sizes.
- Shank hardened to 52 to 57 HRc.
- Zinc-plated body, burnished body.

Information

A [mm] 1,4

d [mm] 3,5

L [mm] 83

L1 [mm] 21

[g] 10

[kg] 0,010

