

Features

- Dielectric strength is 20kV/mm
- Tensile strength at break is 20MPa
- Does not spread flames in the event of a fire
- Operating temperature ranging between -20°C and 90°C

RS Stock No.: RS PRO



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO PVC is constructed with PVC insulation, this sleeve provides effective mechanical protection for electrical cables. It is suitable for conveying fluids under low pressure at ambient temperatures and offers strong resistance to ozone, ageing, acids, and abrasion.

General Specifications

Part Number	Internal Diameter (mm)	Wall Thickness (mm)
0848967	1.00	0.4
0848974	2.00	0.4
0848965	8.00	0.62

