

DURACELL® Lithium Coin Battery

Duracell Batteries (Lithium)

Duracell	IEC	ANSI	Voltage	Overall Ht.(MM)	Overall Ht.(in.)	Diameter (MM)	Diameter (in.)
DL1025	-	-	3.0	2.5	0.080	10	0.394
DL1216	-	-	3.0	1.6	0.063	12.5	0.492
DL1616	CR1616	-	3.0	1.6	0.063	16	0.63
DL1620	CR1620	5009LC	3.0	2.0	0.079	16	0.63
DL2016	CR2016	5000LC	3.0	1.6	0.063	20	0.787
DL2025	CR2025	5003LC	3.0	2.5	0.098	20	0.787
DL2032	CR2032	5004LC	3.0	3.2	0.126	20	0.787
DL2430	CR2430	5011LC	3.0	3.0	0.118	24.5	0.965
DL2450	CR2450	5029LC	3.0	5.0	0.197	24.5	0.965

Duracell	Endpoint Voltage	Typical Capacity (MAh)
DL1025	2.0	30
DL1216	2.0	25
DL1616	2.0	55
DL1620	2.0	68
DL2016	2.0	85
DL2025	2.0	160
DL2032	2.0	230
DL2430	2.0	285
DL2450	2.0	540

DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage.