

Multi Tool LXT®

DTM51

18V

Versatile multi-tool with tool-less accessory clamp

A handy 18V LXT® multi-function tool for a variety of cutting and polishing applications in construction and renovation projects. Equipped with a tool-less accessory clamp and the oscillating rate can be adjusted between 6 000 and 20 000 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Orbits per Minute	6000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,6 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{PA})	79 - 84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding	3,0 m/s ²
Tool weight with battery	2,0 - 2,4 kg
Product Dimensions (L x W x H):	340 x 80 x 122 mm
Sound Power Level (L _{WA})	88 - 92 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Vibration Level, Cutting With Plunge Cut Saw Blade	7,0 m/s ²

User benefits

- Variable speed control dial enables user to match the speed to the application for greater versatility
- Tool-less blade change for fast blade installation and removal
- Soft start for smooth start-ups
- The rubber coating on the handle ensures a firm working grip
- Anti-restart function minimises accidental start-up
- Battery protection system automatically shuts off power when the battery level is low
- 12 Angle settings at every 30° from 0° to 360°

Link to product - www.makitauk.com



Related products

Optional AC

199627-2

Dust attachment set

837671-8

MakPac (3) Inlay

B-21565

Abrasive Paper 94 mm, 60G

B-21587

Abrasive paper 94 mm, 100G

B-21602

Abrasive paper 94 mm, 180G

B-21624

Abrasive paper 94 mm, 60G

B-21646

Abrasive paper 94 mm, 120G

B-21668

Abrasive paper 94 mm, 240G

B-21680

Abrasive paper 94 mm, 60G

B-21705

Abrasive paper 94 mm, 100G

B-21727

Abrasive paper 94 mm, 320G

B-21749

Abrasive paper 94 mm, 120G

B-21761

Abrasive paper 94 mm, 400G

B-21783

Abrasive paper 94 mm, 1200G

B-21808

Fleece Coarse 94 mm, 100G

B-21820

Polishing Felt Hard, 94 mm

B-22947

Abrasive paper 94 mm, 100G



821551-8

Makpac case (3)



B-21559

Abrasive paper set, 94 mm



B-21571

Abrasive paper 94 mm, 80G



B-21593

Abrasive paper 94 mm, 120G



B-21618

Abrasive paper set 94 mm



B-21630

Abrasive paper 94 mm, 80G



B-21652

Abrasive paper 94 mm, 180G



B-21674

Abrasive paper set 94 mm



B-21696

Abrasive paper 94 mm, 80G



B-21711

Abrasive paper 94 mm, 240G



B-21733

Abrasive Paper set 94 mm



B-21755

Abrasive paper 94 mm, 240G



B-21777

Abrasive paper 94 mm, 600G



B-21799

Fleece Medium 94 mm, 280G



B-21814

Cleaning Fleece 94 mm



B-22931

Abrasive paper 240G



B-22953

Abrasive paper 94 mm, 150G



Optional AC

B-22969

Abrasive paper 94 mm, 120G



B-64820-5

Plunge Cut Saw Blade 65 mm



B-64864-5

Plunge Cut Saw Blade 65 mm



B-64886-5

Plunge Cut Saw Blade 32 mm



B-64901-5

Plunge Cut Saw Blade 65 mm



B-65006-5

Joint Cutter Blade 28mm



B-67480

Multi-tool 4 Piece Plunge Cut Set



B-67496

Starlock Multi-tool 4 Piece Saw Set



B-67505

Multi-tool 4 Piece Floor Set



B-67511

Multi-tool 5 Piece Carpentry Set



Other

User manual

Parts drawing