



**B194**

**BahcoFit TORX® Screwdrivers  
with Rubber Grip T4-T45**



PRODUCT DETAILS

- For TORX® head screws
- Black oxide tip for higher accuracy
- Two-component handle with vertical grooves for comfortable grip and maximum force transmission, anti-slip surface
- Handle made with over 75% rubber
- Anti-slip surface
- Permanent symbol and markings on the handle for quick identification of the tip
- Integrated hanging hole
- Chrome plated blade for high protection against corrosion, long life tool
- High-performance alloy steel blade
- SB coding for retailed packed on a plastic hanger



**Follow the Fish!**



## PRODUCT ATTRIBUTES

Product							
<b>B194.004.075</b>	T4	1.30 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm
<b>B194.005.075</b>	T5	1.37 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm
<b>B194.006.075</b>	T6	1.65 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>B194.007.075</b>	T7	1.97 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>B194.008.075</b>	T8	2.30 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>B194.009.075</b>	T9	2.48 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>B194.010.075</b>	T10	2.72 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>B194.015.100</b>	T15	3.26 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm
<b>B194.020.100</b>	T20	3.84 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm
<b>B194.025.125</b>	T25	4.40 mm	125 mm	5 mm	30 mm	105 mm	230 mm
<b>B194.027.125</b>	T27	4.96 mm	125 mm	5 mm	30 mm	105 mm	230 mm
<b>B194.030.150</b>	T30	5.49 mm	150 mm	6 mm	34 mm	117 mm	267 mm
<b>B194.040.150</b>	T40	6.60 mm	150 mm	7 mm	34 mm	117 mm	267 mm
<b>B194.045.150</b>	T45	7.70 mm	150 mm	8 mm	34 mm	117 mm	267 mm
<b>SB194.004.075</b>	T4	1.30 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm
<b>SB194.005.075</b>	T5	1.37 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm
<b>SB194.006.075</b>	T6	1.65 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>SB194.007.075</b>	T7	1.97 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>SB194.008.075</b>	T8	2.30 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>SB194.009.075</b>	T9	2.48 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>SB194.010.075</b>	T10	2.72 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm
<b>SB194.015.100</b>	T15	3.26 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm
<b>SB194.020.100</b>	T20	3.84 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm
<b>SB194.025.125</b>	T25	4.40 mm	125 mm	5 mm	30 mm	105 mm	230 mm
<b>SB194.027.125</b>	T27	4.96 mm	125 mm	5 mm	30 mm	105 mm	230 mm
<b>SB194.030.150</b>	T30	5.49 mm	150 mm	6 mm	34 mm	117 mm	267 mm
<b>SB194.040.150</b>	T40	6.60 mm	150 mm	7 mm	34 mm	117 mm	267 mm
<b>SB194.045.150</b>	T45	7.70 mm	150 mm	8 mm	34 mm	117 mm	267 mm

Follow the Fish!

