

## Features

- **Creates a Secure Lockable Barrier** – Prevents unauthorized entry, animals, and debris from entering confined spaces.
- **Adjustable Cable Locking System** – Integrated cable around the rim can be padlocked for access control.
- **Ventilated Mesh Construction** – Polyester net allows airflow while providing effective visual and physical barrier.
- **OSHA-Compliant Signage** – Includes clear warning signs to notify workers of confined space hazards.
- **Durable & Reusable Design** – Lightweight, easy to clean and store, ideal for repeated use.
- **Universal Fit** – Suitable for a variety of manhole and confined hole sizes.

## RS PRO Lockable Ventilated Confined Space Cover - Large (36" ø)

RS Stock No.: 0694409



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *Lockable Ventilated Confined Space Covers provide effective lockable barrier protection to prevent unauthorised entry.*
- *It fits most entry and egress points on man-ways, heater doors, nozzles and vessel skirts. The lockable and adjustable cover is fitted over the existing flange and is secured by installing a padlock.*
- *Creates a lockable safety barrier to prevent unauthorized access into confined spaces such as manholes.*
- *Outer cable rim features adjustable lockout, allowing padlock application for restricted entry.*
- *Made from durable polyester mesh for visibility and ventilation, with solid flanged sides to reinforce boundary.*
- *Designed to withstand industrial conditions, yet lightweight for easy handling, cleaning, and storage.*
- *Includes OSHA-required caution signage to enhance worker awareness of entry hazards.*
- *Compatible with multiple confined space sizes, commonly used as part of a manhole protection system.*

## General Specifications

<b>Type</b>	Lockable Confined Space Cover Lockout
<b>Material</b>	Nylon Mesh + ABS
<b>Colour</b>	Red & Black
<b>Package</b>	BOPP + Bag

## Mechanical Specifications

<b>Diameter</b>	914mm (36")
<b>Weight</b>	810 Grams

## Operation Environment Specifications

<b>Withstand temperature</b>	-20°C to 80 °C
------------------------------	----------------