

PRODUCT-DETAILS

216RAU4W

216RAU4W Panel mounted socket



General Information

Extended Product Type	216RAU4W
Product ID	2CMA166994R1000
EAN	7392696669948
Catalog Description	216RAU4W Panel mounted socket
Long Description	Socket-outlet, panel mounting, earthing sleeve position 4h, rated current 16A, IP67 watertight, unified flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Yellow

Ordering

E-Number (Sweden)	2416694
E-Number (Finland)	2420146
E-Number (Norway)	1561901
EAN	7392696669948
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	95 mm
Product Net Height	102 mm

Product Net Weight	0.19 kg
--------------------	---------

Container Information

Package Level 1 Width	110 mm
Package Level 1 Depth / Length	110 mm
Package Level 1 Height	110 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	7392696669948
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	116.6 kg
Package Level 2 EAN	7392696071529
Package Level 2 Units	pallet (lift) 420 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	6 ... 13 mm
Color	Yellow
Connection Type	Screw
Degree of Protection	IP67 IP69
Frequency (f)	50 Hz 60 Hz
Function	Socket outlet, panel mounting, unified flange, angled
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#216RAU4W

Mounting Holes	79.5x79.5
Mounting Type	unified flange, angled
Number of Poles	3
Order Multiple	1 piece
Product Main Type	TRAU
Product Name	Panel mounted socket
Protection Type	Watertight
Rated Current (I_n)	16 A
Rated Frequency (f)	50...60 Hz
Rated Voltage (U_r)	100 ... 130 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Socket Outlets for Panel Mounting
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440504
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Socket Outlets for Panel Mounting

