

Datasheet

RS Pro 13A Surface Mount Fused Connection Unit

RS Stock No: **687-7332**



Product Details

RS Pro surface mount fused connection unit has a voltage rating of 230 V ac and current rating of 13 A. It is designed to provide protection against the risk of electrocution and fire hazards. It has a trip current of 30 mA and trip speed of 30 ms. The fused connection unit meets BS7288: 1990 and BS1363 standards.

Features and Benefits

- Current rating of 13 A
- Voltage rating of 230 V ac
- Trip current of 30 mA
- Trip time of 30 ms

Specifications:

Colour	Grey
Current Rating	13 A
Depth	46 mm
Dimensions (L x W x D)	86.5 x 86.5 x 46 mm
Earth Terminal	Yes
Fuse Type	BS 1363, BS 7288
Height	86.5 mm
Length	86.5 mm
Minimum Box Depth	46 mm
Mounting Style	Surface Mount
Number of Poles	2
RCD Type	Passive
Trip Current	30 mA
Trip Speed	40 ms
Voltage Rating	230 V ac
Voltage Rating	230 V ac
Width	86.5 mm