

More than sensors + automation

JUMO heatTHERM


Electromechanical thermostat series





More than sensors + automation

Temperature controllers (TR)




Temperature monitors (TW)



Safety temperature monitors (STW)



Safety temperature limiters (STB)



General data

JUMO heatTHERM - (Type 602031)

Versions	TR/TW/STW/STB
Measuring ranges	See data sheet To customer specification
Sensor diameter	6 mm (standard)
Capillary length	2000 mm standard To customer specification
Contact rating on the normally closed contact	400V AC, 16A 230V AC, 16A
Maximum permissible sensor temperature	max. set value +25K
Permissible ambient temperature	0°C to +80°C (in use) -50°C to +80°C (transport/storage)

Approvals





DGRL97/23/EG

Areas of operation

- Heating and air conditioning industry
- Plastics technology, furnace construction
- Industrial oven construction, climatic test chambers
- General mechanical engineering