



Main

Range of product	Mini Opale
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Nb of 18 mm modules per row	6
Nb of horizontal rows	1
Provided equipment	Terminal block (2)
Width	119 mm
Height	160 mm
Depth	65 mm

Complementary

Enclosure mounting	Surface
Total number of 18 mm modules	6
[In] rated current	63 A
Type of rail	DIN
Number of terminal blocks	2 4
Distribution block outgoers	6 x 10 mm ² 2 x 16 mm ²
Enclosure material	Enclosure : self-extinguishing material
Colour	Enclosure : white (RAL 9003)

Environment

Standards	EN 50102 IEC 60529
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Contractual warranty

Period	18 months
--------	-----------