

FOC-V14-C1ZNI-T/SJFP - FO connectors



1408028

<https://www.phoenixcontact.com/in/products/1408028>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Push-pull connector (version 14), die-cast zinc, with SC-RJ insert for POF, for cable diameter of 5.5 mm ... 10 mm, cable outlet at the top

Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent release
- Highest ESD and EMC resistance for reliable transmission

Commercial data

Item number	1408028
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABN
Product key	ABNOBA
Catalog page	Page 367 (C-2-2019)
GTIN	4046356788427
Weight per piece (including packing)	102.2 g
Weight per piece (excluding packing)	91.249 g
Customs tariff number	85367000
Country of origin	PL

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.4 Connectors for outside environment (optical fibre) and chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data connector (cable side)
Type	SC-RJ
Connection profile	SC-RJ connector
Cable outlet	angled

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Attenuation	≤ 1.5 dB (in accordance with ISO/IEC 24702)
Transmission medium	FO

Dimensions

Width	22 mm
Height	34 mm
Length	80 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Ferrule material	Copper alloy
Housing material	Metal
Housing surface material	nickel-plated

Cable/line

Cable type	Plastic fiber
External cable diameter	5.5 mm ... 10 mm
External cable diameter	5.5 mm ... 10 mm
Resistance to oil	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	980/1000 µm
Fiber type	POF

1408028

<https://www.phoenixcontact.com/in/products/1408028>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Characteristics

Attenuation	≤ 1.5 dB (in accordance with ISO/IEC 24702)
-------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 40 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes

FOC-V14-C1ZNI-T/SJFP - FO connectors



1408028

<https://www.phoenixcontact.com/in/products/1408028>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1408028>



UL Listed

Approval ID: E308814-20180830

FOC-V14-C1ZNI-T/SJFP - FO connectors



1408028

<https://www.phoenixcontact.com/in/products/1408028>

Classifications

ECLASS

ECLASS-11.0	19170122
ECLASS-12.0	19170122
ECLASS-13.0	27440290

ETIM

ETIM 9.0	EC001122
----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

FOC-V14-C1ZNI-T/SJFP - FO connectors



1408028

<https://www.phoenixcontact.com/in/products/1408028>

Accessories

VS-SCRJ-POF-KONFTOOL-POLISH - FO accessories

1658820

<https://www.phoenixcontact.com/in/products/1658820>



SC-RJ polishing tool set, for polymer fiber, for field assembly of the SC-RJ connector (IP20/IP67) with fast connection technology, with stripping tool, diagonal cutter, aramid scissors, polishing materials, microscope, 2x SC-RJ connector IP20

VS-PPC-F1-PC-POBK - Protective cover

1405316

<https://www.phoenixcontact.com/in/products/1405316>



Protective cover, IP65, with push-pull locking for covering the contact insert in the push-pull connector for RJ45 and SC-RJ, plastic

FOC-V14-C1ZNI-T/SJFP - FO connectors

1408028

<https://www.phoenixcontact.com/in/products/1408028>



FOC-V14-F1ZNI-EM/SJB - Panel-mount frame

1413964

<https://www.phoenixcontact.com/in/products/1413964>



SC-RJ panel mounting frame, IP67, for push-pull interlocking, metal, for rectangular mounting cutout, with seal and mounting screws, incl. SC-RJ coupling

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in