

Technical data sheet

Article number:
131-12520

RT250

Product Group	Cable tie outside serrated
Product Family	RT-series up to 190 N loop tensile strenght
Material	Polyamide 12 (PA12)
Colour	Black (BK)
Bundle Ø max.	71.0 mm
Bundle Ø min.	1.6 mm
Flammability	UL 94 HB
Length (L)	250 mm
Min.Tensile Strength	190 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pcs.
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	Yes
Thickness (T)	1.7 mm
Variant	Outside Serrated
Weight/Unit	0.0032 kg
Width (W)	9.0 mm

