

## FEATURES

- **Quality chrome molybdenum vanadium steel material**
- **Comfortable TPR grip and polypropylene injected shafts and handles**
- **Meets the standards of VDE**
- **Insulated 1000V**
- **Heat treated to HRC: 55-59**

## RS PRO VDE Slotted; Phillips; Pozidriv Screwdriver Set 10 Pieces

RS Stock No.: 253-015



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Our RS Pro 10 Piece Insulated Screwdriver Set has been designed and manufactured with durable chrome-molybdenum vanadium steel. The generous sized, easy grip handles are soft to touch and are made up of anti-slip thermoplastic rubber (TPR). Our screwdriver kit has been designed to meet the VDE standards, which means that this set is safe to use when working with electricity making it the perfect option for users that work within an electrical environment. Our RS Pro Screwdriver Kit has a wide variety of tip types, sizes and lengths which offer a solution for most commercial or industrial situations.

## General Specifications

<b>Screwdriver Type</b>	Insulated
<b>Number of Pieces</b>	10
<b>Tip Type</b>	Slotted; Philips; Pozidriv
<b>Set Contents</b>	Pozidriv: PZ1 x 100mm, PZ2 x 125mm
<b>Applications</b>	Household DIY, Electrical and Engineering

## Mechanical Specifications




<b>Tip Size</b>	Slotted: 2.5mm; 3mm; 4mm; 5.5mm; 6.5mm Philips: PH0; PH1; PH2 Pozidriv: PZ0; PZ1
<b>Blade Length</b>	Slotted: 75mm; 100mm; 100mm; 125mm; 150mm Philips: 60mm; 80mm; 100mm Pozidriv: 60mm; 80mm
<b>Blade Material</b>	Chrome Vanadium Steel (8660) for Phillips, Pozidriv and Slotted blades
<b>Handle Material</b>	PP/TPR
<b>Blade Finish</b>	Black Phosphate
<b>Hardness</b>	Heat treated to HRC: 54~58 Degrees for the Screwdriver bits

## Approvals

Compliance/Certifications

VDE



Kit Contents			
Pieces in set	Slotted (mm)	Phillips (MM)	Pozidriv (MM)
10	2.5 x 75 3 x 100 4 x 100 5.5 x 125 6.5 x 150	No.0 x 60 No.1 x 80 No.2 x 100	No.0 x 60 No.1 x 80
Type of bit			

Contents	
Slotted Width x Length (mm)	2.5 x 75; 3 x 100; 4 x 100; 5.5 x 125; 6.5 x 150
Phillips Size x Length (mm)	No.0 x 60; No.1 x 80; No.2 x 100
Pozidriver Size x Length (mm)	No.0 x 60; No.1 x 80