

ENGLISH

Datasheet

RS Pro 200mA Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: 767-5190



Product Details

RS Pro radial non-resettable fuse withstands currents up to 200 mA and voltages up to 250 V. It has thermoplastic body for added durability. This fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- Fast acting fuse
- Non-resettable
- · Radial fuse
- Wire-ended



ENGLISH

Specifications:

| Body Diameter | 8.35 mm |
|---|-------------------------|
| Body Height | 7.7 mm |
| Body Material | Thermoplastic |
| Breaking Capacity (at Maximum Voltage Rating) | 35 A at 250 V ac |
| Current Rating | 200 mA |
| Lead Orientation | Radial |
| Maximum Operating Temperature | +125°C |
| Minimum Operating Temperature | -55°C |
| Voltage Rating | 250 V |
| Voltage Rating | 250 V |
| Wire Diameter | 0.62 mm |
| Wire Length | 22 mm |
| Wire Pitch | 5.08 mm |
| Fuse Type | Fast Acting |
| Nominal Resistance | 0.52 Ω |
| Standards Met | VDE, CSA, UL, CCC, RoHS |
| | |