



TOUGHPAD FZ-Q2

SEMI RUGGED DETACHABLE MOBILE COMPUTER

With shock-absorbing technology and dust resistance, the 12.5" Toughpad FZ-Q2 has been designed to operate in challenging working environments. It offers more protection than a consumer grade tablet without the weight of a fully rugged device. Featuring business interfaces like native serial and LAN it's the perfect companion for white collar field workers. The semi rugged design and large display combined with optimized wireless capabilities enables retail, insurance and telecoms to further improve operation efficiency.

- Intel® Core™ m5-6Y57 vPro™ processor
- Windows 10 Pro
- Intel® HD Graphics 515
- 12.5" high brightness Full-HD (1920x1080) display
- Capacitive 10 finger multi-touchscreen
- 76 cm drop resistant*
- Spillproof backlit keyboard
- up to 9 hours battery life (MobileMark™ 2014)
- Native Serial, LAN, USB 3.0 and HDMI Port
- Balanced weight design - weighs approx. 1,93kg (1,09kg tablet + 0,84kg keyboard including strap & kickstand)

* Tested at Panasonic Factory



Panasonic recommends Windows 10 Pro.

THE FIRST BUSINESS TABLET THAT DOESN'T MIND GETTING DIRTY

The FZ-Q2 offers a rich set of business interfaces (HDMI, native serial and LAN), ships with Windows 10 Pro and is powered by 6th Generation Intel® Core™ vPro™ processor technology targeting field workers, maintenance, service technicians and retailers.



Mobile Computing Platform	Intel® Core™ m5-6Y57 vPro™ processor 1.1 GHz up to 2.8 GHz with Intel® Turbo Boost Technology, 4MB Intel® Smart Cache	
Operating System	Windows 10 Pro Windows® 7 Professional (available through downgrade rights from Windows 10 Pro)	
RAM	4GB RAM	
Graphic Chip	Intel® HD Graphics 515	
Camera	Front:	2 MP
	Rear:	8 MP with autofocus and LED light
Storage	128 GB Solid State Drive (Serial ATA)	
LCD	12.5" Full-HD Active Matrix (TFT) IPS colour LCD	
Touchscreen	10 finger capacitive multi-touchscreen	
Keyboard	Backlit with handstrap and kickstand (english, german or french)	
Bluetooth®	Version 4.1	
WLAN	Intel® Dual Band Wireless-AC 8260	
Mobile Broadband	Optional 4G LTE	
LAN	x1 1000BASE-T / 100BASE-TX / 10Base-T	
Sound	WAVE and MIDI playback, Intel® High Definition Audio subsystem support, Microphone arrays (built-in)	
Interface	USB 3.0:	x1
	LAN Connector:	x1 RJ-45
	Serial:	x1
	HDMI:	x1
	Headset:	x1 (Main Unit)
	Desktop Cradle / Keyboard Connector:	x1
Expansion slots	Micro SD/SDXC Memory Card:	x1 micro SDXC
Power	AC Adapter:	Input: 100V - 240V AC, 50Hz/60Hz, Output: 16 VDC, 3.75A
	Battery:	Li-Ion 7.2 V, 4860mAh (non-removeable)
	Operating Time:	9 hours (MobileMark™ 2014)
Security Features	TPM (Trusted Platform Module, TCG V1.2 compliant), Integrated hardware security lock slot, Password security (supervisor password, user password, HDD lock)	
Physical Dimensions (W x D x H)	340mm x 220mm x 43mm (Tablet + Keyboard) 340mm x 220mm x 19mm (Tablet only)	
Weight	approx. 1.93kg (Tablet + Keyboard) approx 1.09kg (Tablet only)	
Standard Configuration	FZ-Q2mk1 Tablet, Backlit Keyboard, 4GB RAM, 128GB SSD, Capacitive Pen	
Included in Box	AC Adaptor, Power Cord, Tether, Cleaning Cloth, User Manual	
Accessories	Desktop Cradle	FZ-VEBQ11U
	AC Adaptor	CF-AA6373A
	Hand Strap	FZ-VSTQ11U
	Capacitive Stylus	FZ-VNPQ11U
	Protection Film	FZ-VPF066U
	Carrying Solutions	Please visit www.toughbook.eu
Testing Standards	Gravity drop resistance test:	76 cm*
	Operating temperature:	0°C to +50°C -10°C to +50°C with optional SSD Heater
	Storage temperature:	-20°C to +60°C

FZ-Q2mk1: 18.04.2017

* Tested at Panasonic Factory

Intel, the Intel Logo, Intel Core, Intel vPro, Core Inside and vPro Inside are trademarks of Intel Corporation in the U.S. and other countries. Microsoft® and Windows® are registered trademarks of Microsoft Corporation of the United States and/or other countries. All other brand names shown are the registered trademarks of the relevant companies. All rights reserved. All working conditions, times and figures quoted are optimum or ideal levels and may differ as a result of individual and local circumstances.

Computer Product Solutions (CPS) BU, Panasonic System Communications Company Europe (PSCUE), Panasonic Marketing Europe GmbH, Hagenauer Straße 43, 65203 Wiesbaden (Germany).

Panasonic
BUSINESS

www.toughbook.eu