



EN ISO 20345:2011



SKIPPER LADY

BOMA

95401-04L

S3 SRC
Size: 35-42 Lady

Weight: 440 gr.

Fit: 11

Working Environment:

Logistics and Light Industry,
Components and Automotive, ESD
Areas


FEATURES

UPPER

MicroFiber Suede 1,6-1,8 mm
Crack Lamé

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Five 4 Fit "lady"

TOE CAP

Alu SXT 2.0 Toe cap

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Low Shoe

SOLE

PU DUAL-DENSITY SRC

Double density PU outsole with tread designed mainly for indoor use. Self-cleaning design and highly non-slip grip. SRC Antislip standard.

TECHNOLOGIES

Removable Insole



Highly breathable and absorbent anatomic insole. Multilayer structure to take advantage of the peculiarities of each component. Dry and with a comfortable memory foam "pillow"



Protection elements


RESISTANT
TO 3.0 mm.
NAILS

alu-sxt2.0
aluminium

Toecap "Alu Sxt 2.0" with differentiated thicknesses, resistant to 200J. Non metal perforation resistant Insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic **HC** control
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability


STABIL • ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other

DUALMICRO
DUALMICRO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)


SOLE 95
PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE 7°) ≥0.28	0.38
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE 7°) ≥0.13	0.21
		0.24

EN ISO 20344:2011