

# Rittal – The System.

Faster – better – everywhere.



## PK 9502.000

## Polycarbonate enclosures PK

State: 19/07/2022 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9502.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.

## Features

Model No.	PK 9502.000
Applications	Ambient temperature range: -35 °C...+80 °C The specified temperatures may be limited by the installed equipment
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 94 mm Height: 65 mm Depth: 57 mm
Design cover	grey
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	8 pc(s).

# Features

---

Weight/pack	1.104 kg
Copper weight (kg per piece)	0
Customs tariff number	94037000
EAN	4028177139015
ETIM 7.0	EC000261
ECLASS 8.0	27180101

---

# Approvals

---

Approvals	C-UL DNV-GL GOST UL UL + C-UL (listed)
Explanations	Declaration of conformity

---