

## Features

- 1U Panel
- 16 x Dual USB2.0 A-A
- Cable strain-relief bar
- Label strip

## RS PRO 16 Port Dual USB2.0 A-A Connector Rack Patch Panel, 1U

RS Stock No.: 0360705



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



## Product Description

These panels have 16 x 24mm holes to accept feedthrough and other XLR-format connectors. A connector labelling strip is located on the front and a cable strain-relief bar is fitted at the rear. Applications include broadcast and AV patch panels, MIL, medical, control and instrumentation signal input/output panels etc. These pre-assembled panels simplify system assembly, reduce manufacturing time, component count and cost.

This panel is pre-loaded with 16 x Dual USB2.0 A-A connectors.

## General Specifications

Connector Type	Dual USB2.0 A-A
Termination	USB Cables
No of Ports	16
Panel size	1U
Depth	105mm

## Electrical Specifications

FOR USB2.0 CONNECTOR	
Rated Current	1.5A
Rated Voltage	30V
Contact Resistance	≤30mΩ
Insulation Resistance	1000MΩ
Dielectric Strength	500V AC

## Mechanical Specifications

Operating Temperature	-25°C to +85°C
Lifetime	>1500 mating cycles

## Approvals

Standards Met	RoHS
---------------	------



