

**ZMA45/85** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M45X1,5	Thread
D	85 mm	Outside diameter
h	32 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	630,000 N	Breaking load, axial
M _L	110 Nm	Breakawag
M _{AL}	65 Nm	Mounting torque reference
M _M	11.9 kg*cm ²	Mass moment of inertia
≈m	0.993 kg	Weight

Dimensions

d ₁	78 mm	Plant diameter outside
t	3 mm	Hight retaining slot
b	7 mm	Width retaining slot
c	16 mm	Distance bore
m	M8	Threaded - threaded pin