

**Enclosure:**

<b>Material / of the housing</b>		metal
<b>Color / of the top part of housing</b>		yellow

**Actuator:**

<b>Design of the operating mechanism</b>		EMERGENCY-STOP
<b>Material / of the activation element</b>		metal
<b>Manner of function / of the activation element / arresting lock</b>		Yes
<b>Manner of function / of the activation element / tentative</b>		No

**General technical details:**

<b>Product designation</b>		enclosure for control and signaling units with standard fittings
<b>Design of the product / with coat of paint</b>		Yes
<b>Operating current</b>		
<ul style="list-style-type: none"> <li>• at AC-15 / at 230 V</li> <li> <ul style="list-style-type: none"> <li>• at 50 Hz / rated value</li> <li>• at 60 Hz / rated value</li> </ul> </li> <li>• at DC-13 / at 24 V / rated value</li> </ul>	A	6 4 3
<b>Operating voltage</b>		
<ul style="list-style-type: none"> <li>• for DC / rated value / maximum</li> <li>• for DC / rated value / minimum</li> <li>• 1 / for DC / rated value</li> <li>• 1 / at 50 Hz / for AC / rated value</li> <li>• 1 / at 60 Hz / for AC / rated value</li> <li>• at 50 Hz / at AC / rated value / minimum</li> <li>• at 50 Hz / at AC / rated value / maximum</li> <li>• at 60 Hz / at AC / rated value / minimum</li> <li>• at 60 Hz / at AC / rated value / maximum</li> </ul>	V	230 5 230 400 300 5 400 5 300
<b>Type of voltage</b>		
<ul style="list-style-type: none"> <li>• of the operating voltage</li> </ul>		AC/DC
<b>Number of key-operated switches</b>		0
<b>Number of selection switches</b>		0
<b>Number of mushroom pushbuttons</b>		1
<b>Number of control points</b>		1

Number of indicator lights		0
Number of pushbuttons		0
Product function / emergency-OFF function		Yes
Supply status / pre-wired on terminal strip		No
Supply status / as a kit		No
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Item designation / according to DIN EN 61346-2		S
Design of the electrical connection		spring-loaded terminals
Type of fixing/fixation / for switching elements, socket fixing and accessories		floor mounting
Product component		
<ul style="list-style-type: none"> <li>• stand/pedestal</li> </ul>		No
<ul style="list-style-type: none"> <li>• protective collar</li> </ul>		Yes
Color / of the button		red

#### Auxiliary Contacts:

Number of NC contacts / for auxiliary contact		2
Number of NO contacts / for auxiliary contact		0
Number of change-over switches / for auxiliary contact		0

#### Installation/mounting/dimensions:

Type of fixing/fixation		screw fixing
Shape / of the installation hole		round
Mounting diameter	mm	22
Width	mm	85
Height	mm	85
Depth	mm	114

#### Ambient conditions:

Protection class IP		IP67
Ambient temperature		
<ul style="list-style-type: none"> <li>• during the operating phase</li> </ul>	°C	-25 ... 70
Climatic class / according to DIN 50017		KTW24

#### Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Global Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3801-2DU3/all>

**last change:**

Aug 16, 2010