

Stainless steel waterproof clock Ø 35cm

Ref. 11384

orium

USES

Inconournable clock in a pro range.

Waterproof function.

Stainless steel finish



PRODUCT DETAILS

Suitable for indoor and outdoor use.

Completely impervious to dust and dripping.

Excellent readability thanks to its 35.5cm diameter.

Very nice stainless steel finish for a trendy look.

Ideal for large spaces.

TECHNICAL INFORMATION

Colour	Dimensions (cm)	Weight net (gr)	Power supply	Power supply included	Materials	Standards	Instructions	Warranty	EAN code
Inox	35,5 x 4,5 x 35,5	1035	1*LR6	Yes	Inox	CE/ROHS	9 langues	3 years	3661474113848

orium®

Product sheet - 07/04/2026 - Non-contractual photos

The information and specifications are provided for information purposes only; HBF reserves the right to make changes in the interests of product development.
HBF, Z.I Bonzom 09270 Mazères - France - information@groupehbf.com - www.groupehbf.com

DETAILED DESCRIPTION

Thanks to its waterproof finish, this clock integrates perfectly with:

- The external environment: schools, industrial buildings...
- The indoor environment: workshops, swimming pools, gyms, train stations, hotels...

Stainless steel housing: does not fear humidity. IP45.

Diameter 35.5cm. Visibility at 40m.

Mineral protective glass.

Operates in the following conditions: -10° / +50°C.

Exists in radio-controlled motion.

LOGISTICS

Box Height (cm)	37,7	Box Width (cm)	37,2
Box Length (cm)	35	Box Weight (kg)	9,5
Customs HS code	9105210000	Qty per box (units)	5
Unit dimension Height (cm)	6,8	Unit dimension Width (cm)	37
Unit dimension Length (cm)	37	Min order qty (units)	5
Unit Weight (gr)	1650	Packaging type	4C box

PACKAGING

