

## Features

- A long, sharp blade for an even cut on wide cables.
- A built-in cable guide for a perpendicular cut.
- Long-lasting return spring.
- Safety latch to keep jaw closed and protect fingers from blade when not in use.
- Hard glass-filled nylon anvil.
- Pressed-steel handles with ergonomic plastic grips for added comfort.
- Replacement blades available.

## RS PRO 250mm Flat Cable

### Shears

RS Stock No.: 359-548



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

From the trusted RS PRO brand, this ribbon cable cutter is the most efficient way to cut neatly ribbon cables. Unlike most cable cutters and nippers, it has a long, sharp blade for an even cut on flat cables up to 64- way (82 mm wide) 28 AWG on 1.27 mm centres . It also features a built-in cable guide to ensure a perpendicular, crush-free cut that doesn't warp or deform the cable cores.

Used in the computer, IT and data communications industries to cut flat ribbon cables up to 64-way (82 mm wide) 28 AWG on 1.27 mm centres. Ideal for:

- Prototyping.
- Device manufacture.
- IT cable installations

## General Specifications

Type	Flat ribbon cable shears
Height Safe	No

## Mechanical Specifications

Overall Length	250 mm
Material	Flat ribbon cable up to 64 way (82mm wide)
Maximum Cutting Capacity	64-way (82 mm wide) flat ribbon cable.
Finish	Chemically blackened jaws, glass-filled nylon anvil and plastic grips.
Width	45 mm
Weight	0.4kg
Handle Material	Plastic
Replacement Blades	359-554

## Electrical Specifications

Non-Sparking	No
--------------	----

ESD Safe	No
VDE/1000V Approved	No
Working Voltage	No
Tested Voltage	No