


End plate VABE-S1-1R-G12

Part number: 8032670

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Construction width	44 mm
Exhaust-air function	Via throttle plate
Based on standard	ISO 5599-1
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Suitability for vacuum	yes
CE mark (see declaration of conformity)	To EU Low Voltage Directive
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 60 °C
Media temperature	-10 °C ... 50 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 50 °C
Product weight	410 g
Type of mounting	Via through-hole for M6 screw
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 5	G1/2
Note on materials	RoHS-compliant
Material end plate	Die-cast aluminium