

## SOPHIE JJD21

S1 P SRC  
EN ISO 20345:2011  
35 to 42



- Suede leather
- J-DREAM dual density TPU sole

- ❖ Tennis shoes, Blue colour.
- ❖ Suede leather upper, thickness 1.9 / 2.1 mm
- ❖ Upper lining in textile, with honeycomb structure, anti-bacterial.
- ❖ Vamp lining in non-woven fabric. Resists scuffing and acid perspiration
- ❖ **J-Souplesse footbed** : full piece, antistatic and anatomic, is soft polyurethane covered with a special fibre; perforated in the front part for better foot venting, cushioning effect in the heel area
- ❖ Padded collar for extra comfort and better ankle and Achilles tendon protection.
- ❖ Closure by blue laces (90 cm). Padded textile tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
- ❖ Heel stiffener to reinforce the heel seat
- ❖ Stab-resistant **FleXtane™** insole and liner by Jallatte, antistatic, 100 % composite. Sewn directly onto the upper and covering 100 % of the foot for total protection
- ❖ 200 Joules steel toe cap with perforations.

### ➤ J-Dream dual density TPU sole, sporty profile :

#### Slip resistance tests results

EN Standard : EN ISO 20345 : 2011

#### Requirement SRC (SRA+SRB)

**SRA** Test ground : ceramic / lubricant : water and detergent

On flat **0,40** (>0,32) – On the heel **0,39** (>0,28)

**SRB** Test ground steel / lubricant : glycerine

On flat **0,19** (>0,18) – On the heel: **0,16** (>0,13)

- ✓ Abrasion resistance.
- ✓ Highly resistant to oils and hydrocarbons.
- ✓ Heel shock absorption 20 Joules.
- ✓ Anti-static.



|            |   |    |    |    |    |    |    |    |
|------------|---|----|----|----|----|----|----|----|
| Weight     | Gross weight (38) : 978 g / Net Weight (38) : 760 g |    |    |    |    |    |    |    |
| Size       | 35  | 36 | 37 | 38 | 39 | 40 | 41 | 42 |
| Packaging  | 10 pairs  |    |    |    |    |    |    |    |
| Dimensions | 600 x 405 x 320                                     |    |    |    |    |    |    |    |