



Lighting **excellence**



@4liteuk



@4liteuk



@4lite




@4liteuk

Tironi CCT

Tironi CCT Wallpack
Code: 4L2/3213

Application Commercial, Industrial



Product Features

- All polycarbonate construction ideal for coastal and adverse weather applications
- Selectable CCT between 3000K, 4000K and 6500K output
- Photocell and sensor options
- Multiple conduit entry and BESA box fixing points
- Supplied c/w optional trim attachment which provides a more commercially aesthetic appearance

Technical Information

Wattage	15W/26W
Lumens Delivered	2300lm (4000K)
Lm/W	91lm/W (4000K)
Beam Angle	80
CRI	80
CCT	3000/4000/6500K
Input	220-240V
Operating Temp	-10°C - 40°C
SDCM	6
Product Weight without Packaging	0.988 kg

Technical Information

Light Source	LED
Colour / Finish	Black
IP Rating	IP65
Class Protection	2
Internal / External	External
Lumen Depreciation	L80 60,000h
Warranty (Years)	4
CE Mark	Yes
Diameter	0 mm
Height	101 mm