



JET3 S3 SRC

CONSTRUCTION

Low-cut shoe with robust construction for optimum durability

Foot protection



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Dual-density outsole



Performance

- Ladder side grip: sole design for good grip on ladders
- High stability ensured by the sole's grip properties



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S3 WRU FO A E SRC

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Events & scenic
- Light industry
- Maintenance

Protects against risks



Antistatic



Shock



Slip



Perforation



JET3 S3 SRC

CONSTRUCTION

Low-cut shoe with robust construction for optimum durability

Foot protection

Standards - Details

Technical details

Shoe type	Low shoe
Outsole material	PU, 2d
Anti-perforation insert	Stainless steel
Upper material	Leather
Upper finition material	Croupon, Pigmented, Water repellent
Safety toe-cap	Stainless steel
Lining material	Textile, Mesh polyamid
Footbed material	EVA, Polyester
Footbed caracteristic	Removable, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	570
Size range	36 → 48



JET3 S3 SRC

CONSTRUCTION

Low-cut shoe with robust construction for optimum durability

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
JET3S3NO36	Black	36	JET3 S3 SRC	3295249242961	13295249242968	10	1	13.03 kg	43.5 cm	59.5 cm	34.0 cm
JET3S3NO37	Black	37	JET3 S3 SRC	3295249243227	13295249243224	10	1	13.5 kg	41.4 cm	57.6 cm	32.2 cm
JET3S3NO38	Black	38	JET3 S3 SRC	3295249243234	13295249243231	10	1	13.7 kg	44.8 cm	55.8 cm	31.4 cm
JET3S3NO39	Black	39	JET3 S3 SRC	3295249243241	13295249243248	10	1	13.8 kg	41.8 cm	57.8 cm	32.0 cm
JET3S3NO40	Black	40	JET3 S3 SRC	3295249243258	13295249243255	10	1	14.9 kg	40.6 cm	58.6 cm	31.6 cm
JET3S3NO41	Black	41	JET3 S3 SRC	3295249243265	13295249243262	10	1	15.3 kg	60.4 cm	43.8 cm	34.4 cm
JET3S3NO42	Black	42	JET3 S3 SRC	3295249243272	13295249243279	10	1	15.3 kg	44.6 cm	60.8 cm	34.0 cm
JET3S3NO43	Black	43	JET3 S3 SRC	3295249243289	13295249243286	10	1	15.9 kg	44.0 cm	60.4 cm	33.6 cm
JET3S3NO44	Black	44	JET3 S3 SRC	3295249243296	13295249243293	10	1	16.3 kg	43.8 cm	60.2 cm	34.2 cm
JET3S3NO45	Black	45	JET3 S3 SRC	3295249243302	13295249243309	10	1	18.0 kg	47.8 cm	65.6 cm	35.6 cm
JET3S3NO46	Black	46	JET3 S3 SRC	3295249243319	13295249243316	5	1	9.0 kg	26.2 cm	64.6 cm	35.6 cm
JET3S3NO47	Black	47	JET3 S3 SRC	3295249243326	13295249243323	5	1	9.5 kg	25.8 cm	64.2 cm	36.4 cm
JET3S3NO48	Black	48	JET3 S3 SRC	3295249243333	13295249243330	5	1	10.2 kg	69.4 cm	29.8 cm	38.2 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height