

Datasheet

RS Pro 7m Extension Reel, 0 Socket With Auto Rewind, Unwound Current Rating 10A, 230 V IP42

RS Stock No: **286-6767**



Product Details

RS Pro heavy duty cable extension reel has a lightweight plastic protective casing for added durability and impact-resistant. This extension cable is 7 m long and has PVC outer sheath for added protection. The cable is voltage rated for 230 V ac and current rated for 10 A. The spring return cable reel has IP42 rated protection and is suitable for manual and machine operated applications. The strength and safety characteristics of the designs ensures suitability of the product for daily rigorous usage, for a wide variety of applications including power tools, vacuum cleaners, lighting and most other types of electrical appliances.

Features and Benefits

- Diecast aluminium protective casing for added durability
- 7 m long
- PVC outer sheath for added protection
- Voltage rated for 230 V ac and current rated for 10 A
- IP42 rated protection to work under most hazardous conditions

Specifications:

Auto Rewind	Yes
Current Rating (Unwound)	10 A
Housing Type	Cassette Reel
IP Rating	IP42
Number Of Cores	3
Number of Sockets	0
Reel Length	7 m
Sheath Colour	Black
Sheath Material	PVC
Voltage Rating	230 V
Dimensions	310 x 290 x 145 mm

