



flow control plate

VABF-S4-1-F1B1-C

Part number: 540175

FESTO

For valve terminals VTSA and VTSA-F, standard port pattern to 15407-2, for mounting between manifold sub-base and valve, for restricting exhaust air ports 3 and 5 on the valve.



Data sheet

| Feature | Value |
|---|---|
| Width | 26 mm |
| Based on the standard | ISO 15407-2 |
| Assembly position | Any |
| Operating pressure | -0.9 ... 10 bar |
| CE mark (see declaration of conformity) | to EU directive low-voltage devices |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| Protection class | IP65 NEMA 4 |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 320 g |
| Vertical stacking type of mounting | on manifold block on individual sub-base |
| Material housing | Aluminium die cast |