

Endress+Hauser TMT84-A1A2A

iTEMP TMT84, Transmitter PA



Picture for reference only. Product appearance may vary based on configuration

Dual sensor input. Advanced diagnostics: sensor monitoring. PROFIBUS PA Profile 3.02.

Configuration of TMT84-A1A2A:

| | | |
|------------------------|----|---|
| Approval: | A1 | Non-hazardous area |
| Output Signal: | A | PROFIBUS PA |
| Electrical Connection: | 2 | Screw terminals, housing form B, DIN EN 50446 |
| Field Housing: | A | W/o, mounting set DIN terminal head |

Alternative part number: TMT84-1020/0