



**Part Number :** [1300100102](#)  
**Product Description :** Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 1.0m (3.28') Length  
**Series Number :** 130010  
**Status :** Active  
**Product Category :** Circular Industrial Cordsets  
**Engineering Number :** 115030K13M010



Documents & Resources

**Drawings**  
[1300100102\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Relevant                                   |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21             |
| REACH SVHC         | Contains Lead per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863  |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                                                                                                                       |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                |
| Category     | Circular Industrial Cordsets                                                                                                          |
| Series       | 130010                                                                                                                                |
| Description  | Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 1.0m (3.28') Length |
| IP Rating    | IP67                                                                                                                                  |
| Product Name | Mini-Change                                                                                                                           |
| Protocol     | DeviceNet                                                                                                                             |
| Type         | Double Ended                                                                                                                          |
| UPC          | 78678808217                                                                                                                           |

#### Agency

|    |         |
|----|---------|
| UL | E152210 |
|----|---------|

#### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum             | 600V |

#### Physical

|                      |                 |
|----------------------|-----------------|
| Cable Diameter       | 12.70mm (.500") |
| Cable Length         | 1.0m (3.28')    |
| Color - Cable Jacket | Yellow          |
| Connector End A      | Mini-Change     |
| Connector End B      | Mini-Change     |
| Coupling Style       | Threaded        |
| Gender               | Female-Male     |
| Keyway               | Single          |
| LED Indicator        | None            |

|                               |                         |
|-------------------------------|-------------------------|
| Material - Cable Jacket       | TPE                     |
| Material - Connector Body     | TPE                     |
| Material - Contact            | Copper Alloy            |
| Material - Coupling Nut       | Black Epoxy Coated Zinc |
| Material - Plating Mating     | Gold                    |
| Net Weight                    | 226.000/g               |
| Orientation                   | Straight to Straight    |
| Poles                         | 5                       |
| Temperature Range - Operating | -20° to +105°C          |
| Wire/Cable Type               | TC-ER                   |
| Wire Size (AWG)               | 16                      |