



Waterproof cut resistant glove, level C, fully dipped with latex free cuff.

TEGERA® OIL GRIP 8858



[Learn more](#)

CUT C GLOVE FOR SUPERIOR NITRILE GRIP IN OILY ENVIRONMENTS

This glove offers superior nitrile grip in oily environments. Waterproof cut resistant glove, level C. Fully and triple-dipped with nitrile foam in palm and a latex free cuff. Re-enforcement between thumb and index finger. 18 gg knitted liner including CRF® cut resistant technology and contains 30% recycled polyester. Touchscreen functionality. Oeko-Tex approved. Withstands contact heat up to 100°C/212°F. Wide size range.

CHARACTERISTICS

- Durable
- Good fingertip sensitivity
- Flexible
- Comfortable
- Excellent grip in oily environments

FUNCTIONS

- Withstands contact heat up to 100°C
- Waterproof
- Anatomically designed
- For touchscreen
- Oil and grease resistant
- Extra long
- Reinforcement between index finger and thumb
- Windproof



PREVENTS RISK OF

Cut injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping, contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, wet environments, oily and greasy environments, dirty environments, harsh environments

PRIMARY AREAS OF USE

Building and construction, construction, engineering, installation work, metalwork, paper industry work, repair work, sheet-metal work, shop work

PRIMARY INDUSTRIES OF USE

Agriculture, mining, oil, gas, petrochemical, pulp and paper, glass, bricks, concrete, metal fabrication, machinery and equipment, mro, automotive, transportation, utilities, building and construction

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves

CATEGORY Cat. II

COLLECTION Oil Grip

LINING MATERIAL 18 gg, CRF® Technology, Glass fibre thread, HPPE, Recycled polyester, Spandex, Stainless steel fibre yarn

LENGTH 260-290 mm

DEXTERITY 5

GRIP DESIGN Foam grip pattern

COLOUR Black

PAIRS PER: BUNDLE/CARTON 6/72

DISPLAY TYPE Bulk pack

DIPPING Fully dipped, Triple-dipped

DIPPING MATERIAL Nitrile, Nitrile foam

CUFF STYLE Extended knitwrist cuff

CUFF MATERIAL Textile

CUT RESISTANCE (EN ISO 13997) Cut resistance level C

CUT RESISTANCE (EN ISO 13997) TDM: 14.5 N

INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Recycled polyester, Stainless steel fibre yarn, Glass fibre thread, Elastane

OUTER MATERIAL SPECIFICATION Nitrile


COMPLIANCE



TP TC 019:2011



EN 407:2020 (No flame protection) X1XXXX



EN ISO 21420:2020

EN 511 cl. 4.3 Water penetration (ISO 15383): Pass



Contact heat rating valid for palm area only

Note: This product needs a few minutes of oil contact to activate the oil grip.

FEATURES



For touchscreen



Waterproof



Windproof



Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	8858-6	7340118473826
7	S	8858-7	7340118473970
8	M	8858-8	7340118474120
9	L	8858-9	7340118474274
10	XL	8858-10	7340118474427
11	XXL	8858-11	7340118474571
12	3XL	8858-12	7340118474724

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com