



PRODUCT-DETAILS

UPS PowerValue 11LI Pro 1000 VA

UPS PowerValue 11LI Pro 1000 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Pro 1000 VA
Product ID	4NWP100177R0001
EAN	7640169262678
Catalog Description	UPS PowerValue 11LI Pro 1000 VA
Long Description	VI UPS PowerValue 11LI Pro 1000VA/700W:230V:50/60Hz:pure sinewave:6 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004322
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	cc1c2097-a9b0-4b46-9ebb-565f3d0fceb7 Switzerland
Simplified SCIP	83d66f91-5a30-416a-a3c0-b51e181a55bb Germany 7e920fc2-4c85-4e33-88e0-392bd2f7e9c5 Germany f0fa8059-4b24-4fc3-acd6-b55a081eb083 Poland 54501ec4-bb78-409f-ad17-15a38929372c Norway b7af7b6c-c35a-47bf-a627-29d04b33bfe1 Finland a1ca1eb7-a326-482f-9325-ba2fe6b0ce0b Netherlands

0dbdd6b7-bbe7-4a34-bbb7-7359d97c80fd	Germany
9089dd0c-b118-43cf-9810-54ff2181fdf1	Denmark
ef3b7ac0-edad-4d76-95e2-42a32fcd30d	Croatia
3a485796-e78a-4edb-b60e-3cfac2c1b265	Czech Republic
7d6f97fa-f16e-4d5f-b103-8d57810e5119	Poland
260f1297-852f-4e9f-9500-8a0ec4a62d5c	Netherlands
d8b99f6b-ae8-4e1d-b488-75a9fb061b7b	Netherlands
bf9ff087-da13-4e26-8b1e-8579d9b365bd	Estonia
5cdd0e75-0bc5-489d-a953-7636c6370a5e	Greece
95c47c5e-c8a5-4172-8787-b708532a0eee	Portugal
48951e9e-3a8d-4173-8121-14ce2032851a	Bulgaria
243bfa15-2e6c-4853-8ad5-0a8968e84108	Sweden
5c290af9-5be0-4719-a8aa-ae22576df85e	France
e32425fb-c0a7-42de-a0dd-e99acfd13263	Poland
3e662b2e-1821-4136-9b7a-097d546ec583	Sweden
dff23696-f5d4-409d-8f60-ab34c2a35315	Germany
b7b0f622-ad43-4c23-b7e5-126976fe2079	Germany
2f65c3a3-483d-4541-9fae-2a12004fa8d8	France
6fc8cd66-bff2-4a55-aff6-7529dde57180	Netherlands
890f26cf-24dc-4df0-ac29-628f6c00a7f	Spain
ae91e210-d3db-49fe-a1e8-077ac9b02ded	Netherlands

Popular Downloads

Data Sheet, Technical Information	4NWD004444_ML
Instructions and Manuals	4NWD004444_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408631
E-Number (Norway)	6600719
Country or Territory of Origin	China

Dimensions

Product Net Width	146 mm
Product Net Height	205 mm
Product Net Depth / Length	395 mm
Product Net Weight	8 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	236 mm
Package Level 1 Height	297 mm
Package Level 1 Depth / Length	496 mm
Package Level 1 Gross Weight	10.5 kg
Package Level 1 EAN	7640169262678

Technical

Apparent Power Output	1000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.1 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U_{in})	230 V
Input Voltage Type	AC
Number of Batteries	2
Number of Outputs	C13 Connection 6
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	600 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004322

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

