

677/C
Break-back torque wrenches

UNI EN ISO 6789

art.	Nm	Kgfm	lbf.ft	D mm	A mm	L mm	kg	mm	
006770607	677/C600	120÷600	12÷60	100÷450	69	55	1059	6,0	10
006770612	677/C800	200÷800	20÷80	150÷600	69	55	1319	6,7	10
006770616	677/C1000	300÷1000	30÷100	200÷750	69	55	1554	7,4	20
006770621	677/C1500	700÷1500	70÷150	500÷1000	69	55	1869	9,6	25



677/1500

